

Download Manual For Sorvall Rc 3c

Thermo Scientific Sorvall RC6 Plus

Thermo Scientific Sorvall RC6 Plus iii P This manual is a guide for the use of Thermo Scientific Sorvall RC6 Plus™ Superspeed Centrifuge Data herein has been verified and is believed adequate for the intended use of the rotor. Because failure to follow the recommendations set forth in this manual could produce personal injury

Sorvall RC

The RC-3C Plus operates at speeds ranging from 150 to 6000 rpm. For More Information. For further information on the Sorvall RC-3C Plus centrifuge and other refurbished centrifuges we can make available, please check our online store.

Sorvall RC

The Sorvall RC 3C Plus low speed, refrigerated centrifuge features large capacity, quiet, and low-heat operation with time-tested drive and refrigeration systems. Its automatic rate control system improves resolution and separation rates by providing smooth and efficient operations, while automated RCF determination enhances accuracy.

Now with brushless motor! SORVALL RC

SORVALL® RC-3C Plus and RC-3B Plus lowspeed, refrigerated centrifuges offer the highest level of reproducibility and reliability. SORVALL® centrifuges have been an industry standard for quality and reliability for over 50 years. Whether at work in a clinical laboratory, a blood bank, a university or an industrial setting, SORVALL®

Sorvall

Sorvall RC-3B, which is an improved version of Sorvall RC-3, offers unsurpassed handiness, efficiency, and exceptional flexibility required in today's lab test centers. DuPont Sorvall RC-3B featuring H6000 rotor and buckets (6 place x 1 liter), can reach up to a maximum speed of 6,000 rpm.

Sorvall RC

Sorvall RC-3C Plus, similar to that of all other centrifugal systems of Sorvall, is incorporated with a range of built-in safety and environmental features such as SUVA® CFC-free refrigerants. The RC-3C Plus operates at speeds ranging from 150 to 6000 rpm.